


- Samples can deviate in the execution from the serie.




Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking !

The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment.
For further details we refer to our webpage: www.renata.com/downloads/restriction_of_use

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

Rev.	①	12.09.2019	SRi	Rev.	⊙	.	.		Customer's Approval			
Rev.	⊙	.	.	Rev.	⊙	.	.		Date			
Rev.	⊙	.	.	Rev.	⊙	.	.		Signature			
Titel: CR1620SM								Scale 2:1	Drawn	05.11.07	SRi	
									Checked	13.09.19	HSn	
									Approved	16.03.19	MDi	
renata batteries								CH-4452 Itingen Switzerland		3.9197.4-1		