



**Take-Along Pump:**

- “One-Touch” one-handed operation frees operator’s hands for use
- Locking pump will not leak when engaged - suitable for travel
- Patented one handed operation frees operator’s hands
- Precision machined valves for a smooth consistent operation
- Cam-lock hinge keeps lid open and closed, reduces odors
- No silicone or latex - perfect for ultra clean environments
- Compatible with any 38-400 threaded neck container
- Dispenses approximately 0.2cc of liquid with each pump

<b>Pump Material</b>	Stainless-Steel
<b>Locks for Travel</b>	Yes
<b>Neck Size / Thread</b>	38-400
<b>Lid-Type</b>	Cam-lock hinge lid
<b>Gasket Material</b>	F217 Tri-Seal Foam

**Pump Care:**

Some types of fluids may leave a residue in the mechanism of the dispenser. Over time, this can reduce the performance of the pump.

Occasional cleaning is recommended to maintain your unit to original efficiency.

Clean by flushing the mechanism thoroughly with warm soapy water. Flush the mechanism again with clean water to remove any soap residue. Do not boil or steam the dispenser. For long periods of inactivity, pumps should be flushed free of liquid and stored inverted in a dry place.

**Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions:**

Before using, users shall determine the suitability of the product for their intended use, and users assume all risk and liability whatsoever in connection therewith. See the Menda Terms and Conditions - [Mendapump.com/Terms-And-Conditions.aspx](http://Mendapump.com/Terms-And-Conditions.aspx)

Specifications and procedures subject to change without notice. *Unless otherwise noted, tolerance is ±10%.*

**TAKE-ALONG PUMP, LOCKING**

3651 WALNUT AVE., CHINO, CA 91710  
 PHONE: (909) 627-2453  
 WEBSITE: [MendaPump.com](http://MendaPump.com)

**DRAWING NUMBER**  
35700

**DATE:**  
Aug.  
2016

