

## Mega Sample Kit

### MS12 15102

Max Dia = 13.5mm  $\pm$  15%

R@25°C = 150 $\Omega$   $\pm$  25 %

SSI = 2.0 A

Energy = 100 J

### MS15 30004

Max Dia = 17.0mm  $\pm$  10%

R@25°C = 30.0 $\Omega$   $\pm$  25%

SSI = 4.20 A

Energy = 120 J

### MS22 10008

Max Dia = 22.0mm  $\pm$  10%

R@25°C = 10 $\Omega$   $\pm$  25%

SSI = 8.00 A

Energy = 200 J

### MS22 50004

Max Dia = 22.0mm  $\pm$  10%

R@25°C = 50.0 $\Omega$   $\pm$  25%

SSI = 4.00 A

Energy = 240 J

### MS35 10018

Max Dia = 35.0mm  $\pm$  10%

R@25°C = 10.0 $\Omega$   $\pm$  25%

SSI = 18.00 A

Energy = 500 J

### MS32 10015

Max Dia = 31.0mm  $\pm$  10%

R@25°C = 10.0 $\Omega$   $\pm$  25%

SSI = 15.00 A

Energy = 250 J