



Feature -

noiseless, conductive rubber
light click feeling
full color LED illuminated avails
long electrical life cycles

Application -

audio / video products
instrumentation
communication equipments

► **SPECIFICATIONS**

SWITCH SPECIFICATIONS	
POLE - POSITION	OFF - <ON> for Momentary Type , SPST
CONTACT RATING	1mA 20V DC
CONTACT RESISTANCE	200Ω MAX.
INSULATION RESISTANCE	100 MΩ min. 100 V DC
DIELECTRIC STRENGTH	Breakdown is not Allowable ; 250 V AC for 1 Minute
OPERATING FORCE	160 ± 40 gf
OPERATING LIFE	500,000 cycles
OPERATING TEMPERATURE RANGE	-20°C ~ 70°C
TOTAL TRAVEL	1.6 ± 0.3 mm

LED SPECIFICATIONS				
ATTENTION (+) ○ — (○) — (○) (-) LEDs are Electrostatic Sensitive devices	Unit	Value / LED Color		
			Ultra Green	Ultra Yellow
FORWARD CURRENT	If	mA	20	20
REVERSE VOLTAGE	Vr	V	5.0	5.0
REVERSE CURRENT	Ir	μA	10	10
FORWARD VOLTAGE@20mA	Vf	V	2.1-2.5	2.0-2.5
LUMINOUS INTENSITY@20mA	Iv	mcd	60	120


■ Physical and electrical information of LED will be provided upon customer's request on switches .

► **HOW TO ORDER**


TC016	-	A	S1	-	RGB			-			
		CAP		LED COLOR		LED COLOR		DIFFUSER PLATE COLOR		CAP SYMBOL	
		S1	S1 TYPE	B BLUE		B BLUE		☐	WHITE (std.) or without cover	Please refer to appendix 1 (knob)	
		S2	S2 TYPE	G GREEN		G GREEN		R	RED	For example	
		S3	S3 TYPE	R RED		R RED		G	GRAY	K3	PK3:Printing
		X	WITH OUT	W WHITE		W WHITE		B	BLUE	E1	PE1:Printing
				Y YELLOW		Y YELLOW		Y	YELLOW	E1:Laser carving	
				RGB FULL COLOR		☐ WHEN RGB		N	GREEN	☐ WITHOUT	
				X WITHOUT		X WITHOUT		W	WHITE (When indicate the cap color)		
										</	

▶ DIMENSION


TC016-AX□□□□




TC016-AS1□□□□




TC016-AS2□□□□




TC016-AS3□□□□



▶ CIRCUIT



▶ P.C.B LAYOUT



▶ MATERIAL

- ACTUATOR : POM
- TERMINAL : BRASS GOLD PLATING
- FRAME : STEEL PLATE
- SPRING : STAINLESS STEEL

	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
A	0	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19
B	A	B	C	D	E	F	G	H	I	J	CH5	CH6	DSK	PIP	C-KEY	CUT	TAKE	REC	ENG	PROD
C	K	L	M	N	O	P	Q	R	S	T	REPLAY	RET1	RET2	KEY ON	AUTO TAKE					
D	U	V	W	X	Y	Z	POWER	ON OFF	ON	OFF		USER A	USER B	USER C	USER D	USER E	USER F	USER G	USER H	USER I
E	OK		Auto	Enter	Start	STOP	OPEN	CLOSE	Exit	Move	USER J									
F	SET	Reset	Light	Alarm	Menu	Next	Back	Delete	Motor	Save										
G	Up	Down	Right	Left	Test	End	Insert	Lock	Print	+/-										
H	ESC	BC	HOME	Health	D-LED 2	OC GENIE	VIDEO INPUT	clr CMOS	Green Power	Save OK										
I	B/R +	Undo Cancel	T/L -	F1	F2	F3	F4	F5	F6	F7										
J	F8	F9	F10	F11	F12	F13	F14	IN 1	IN 2	IN 3										
K	IN 4	IN 5	IN 6																	
L	+	-	x	÷	=	↑	→	▲	▶	▶▶										
M																				
N	↑	→	▲	◀	▶	◀	▶	◀	▶	◀										
O																				
P																				
Q	ME3	ME4	BGND 3D DVE1	BGND 3D DVE2	BUS COLOR	ME BUTTON LINK	*	INSERT	WIPE											
R	⏮	ALL		VP		COPY		RECORD MODE	↑											
S			MUTE																	
T			group																	
U			chair																	
V			OC			CLEAR	CROSS WIND	AMMO TEMP	BARO PRESS	AIR TEMP										
W	BORE-SIGHT	CANT	LEAD	RANGE	MRS	ZERO	TEST	UD	LR											
X	ID	Disp	MF	GALL		BAND	SETUP	MODE	LINK	FUNC										
Y	SHIFT					DEL														
Z				RUN	2D	3D	CH1	CH2	CH3	CH4										