


- Samples can deviate in the execution from the serie.



Tab material: Isotan (54%Cu,44%Ni,Mn)

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely

All framed values will be used for dimension checking !

Rev.	☐			Rev.	☐			 	Customer's Approval			
Rev.	☐			Rev.	☐				Date			
Rev.	☐			Rev.	☐				Signature			
Titel: CR1616SM								Scale 2:1	Drawn	05.11.07	SRi	
									Checked	06.11.07	BBö	
									Approved			
renata batteries 								CH-4452 Itingen Switzerland		3.9196.4-		